

Aidalarm Polished Brass and accessories




The Polished Brass, flush mount Disabled Person Toilet Alarm has been designed for more prestigious locations. AIDALARM meets the growing demand for an emergency signalling system for disabled persons. Everything is available to deliver an effective, fully compliant, simple to install and simple to use system. The A600FBR requires a 12vdc power supply which is available separately.

- DDA Compliant
- BS 8300 Compliant
- High Power Piezo Sounder
- 12 vdc Powered
- Audible & Visual Signalling
- Range of Accessories
- Remote Signalling Output

How the Aidalarm works:

- The Aidalarm controller should be sited where staff are located who can respond to an emergency call.
- Ceiling pull cord and optional Dado panic strip or call buttons are situated in the toilet or other area where assistance may be required.
- Pulling the cord or pressing the panic strip/call button generates an immediate audible/visual alarm at both the WC and at the control panel. An LED illuminates on the pull cord giving the caller reassurance the call has been placed.
- The call can be silenced by pressing the button on the front of the control panel.
- The audible indicators at the WC will bleep every 5 seconds to re-assure the caller.
- Should the cord be pulled again while in the silenced state, the system will call again.
- Non-attendance will cause the panel to bleep every 40 seconds as a warning.
- The system can only be reset by the Press to Reset button located at or near the point of call.




A600FBR Aidalarm Controller



Dimensions mm

Bespoke Back Box 164 x 100 x 55mm



Polished Brass Flush single gang plates and accessories



S1708BR Reset Button



S1705BR Call Button



S1600-R Ceiling Pull Cord



S1778BR Overdoor indicator & buzzer



RPD01000 Dado Panic Strip 1000mm



Hoyles Electronic Developments Ltd

T. 01744 886600

F. 01744 886607

E. sales@hoyles.com

W. www.hoyles.com

