

## Cig-Arrete

CSA-FGV24

The Cig-Arrête® SD Evolution is the first product to incorporate Multiple Detection Technology. Incorporating Flame and Smoke detection it is designed to provide voice messages in any area of a facility to warn of smoking. The CSA-FGV24 will detect cigarette smoke and a 25mm flame at a distance of 6 metres within 1 second. Ordinarily placed inside toilet/washroom or anywhere where illicit smoking is suspected such as rest rooms, schools, hospitals and business.

Fully programmable with a simple hand held remote CSA-IR2, the Cig-Arrête® SD Evolution product range is a truly global product with the ability to play any audio file in any language without the need for complex programming knowledge.



**Dimensions** 197L x 127W x 28.5H mm  
Weight 0.6kg



ALL of the SD Evolution units require a CSA-IR2 remote control.

**One CSA-IR2 can control multiple units.**

**You do not need one remote per unit.**

### Benefits

- Senses flame/smoke
- Plays pre-programmed voice files
- Can be powered by 24Vdc or AA batteries
- Up to 100 messages can be programmed
- Selectable time delays between messages
- Hi-Resolution voice playback
- Detects cigarette smoke and a 25mm flame at a distance of 6 metres within 1 second
- Manufactured in the UK

### Product Features

- On sensing the presence of a flame or smoke, Cig-Arrête® SD Evolution CSA-FGV24 will play any pre-programmed voice files in any language.
- Time delays between messages are selectable via the remote programmer to ensure that the message is broadcast at the right time.
- Up to 100 messages can be pre-programmed and selected either individually or sequentially where each message in the list is played in turn on each activation.
- Cig-Arrête® SD Evolution contains a Windows® based file structure which allows simple 'drag and drop' file copying for ease of programming.
- New SmartWave© hi-resolution voice playback software produces crystal clear hi-fidelity audio files to be broadcast in any location.
- Cig-Arrête® SD Evolution can be powered simply by 8-28Vdc or by 4 x AA batteries (not supplied).